



These wagons are internationally registered for use in mainland Europe only.
2 sliding walls per wagon side gives access to the complete floor area from both sides and facilitate loading/unloading from ground level. The wagon has been designed for an even distribution of the load on the wagon floor.
The maximum wheel pressure on the board is 5 tonnes.
The wagon is fitted with fixing points along both sides for load security purposes.



Wagon Data

Overall length (over buffers)	22.130mm
Overall height	4.280mm
Loading length	20.872mm
Loading width	2.780mm
Loading area	58m²
Loading capacity	157m³
Length of door openings (2 per side)	10.366mm
Height of door openings	2.500mm
Platform height	1.200mm
Tare weight	25.000 kgs
Payload ca.	55.000 kgs
Minimum curve	75 metres
Maximum speed	100 kph

Refer to separate table for height and width dimensions

Payload	A	B	C	
S	39	47	55	**

GE103

Habis 2