

Regina, SK Service Shop

SHOP CAPABILITIES

Car Types

- Tank
- Box
- Coal
- Gondola
- Hoppers including PD

Rebuilding Projects

- M-214 truck re-conditioning
- Rule 88
- 70 to 100 ton truck change-outs
- Conversions
- Life extensions

Exterior Painting

- Complete
- *Capacity to paint 10-25 cars per week*

Linings

- Complete, including tank car
- Excluded linings: rubber
- *Capacity to line 2-5 cars per week*

Project Work

- M-214
- Box car roof conversions
- Hopper roof conversions/gate change-outs

Tank Cars

- Shop certified by AAR to repair, alter and convert carbon steel tank cars
- Certified to perform HM-201 re-qualification tests
- Stub sill (SS-3) Inspection

Tank Cleaning

Cars should be RCRA empty before sending in unless prior arrangements are made with Plant Manager. Check prohibited and excluded commodity list.

Safety Valve Testing

Safety valve test and rebuild if necessary

Other services

- Mobile repair capability
- Ultrasonic thickness and corrosion testing
- Prepares AAR bills – electronic billing available
- Contract Inspections performed (reports, quotes, evaluations)
- Digital camera pictures of car condition emailed at request
- M-1003 Quality assurance certified shop
- AAR Category II and Category III certified
- QA-GEWI
- M1002 certified

Address: Pinkie Road, PO Box 3568
Regina, SK

**Delivering
Line Railroad:** Canadian National

**Frequency
of Switching:** 5 times per week

Telephone: 306-525-0122

Fax: 306-757-2194

E-mail: robert.ripley@ge.com

