

Advanced thinking that's

growing capabilities

The acceleration of new developments in additive manufacturing continues to deliver on the promise of this transformative technology. GE continues to be at the forefront of additive technology as we enable a new phase of high-volume industrial production.

Setting the pace is GE Additive's Arcam EBM Spectra H. With an extended build platform and capability to produce parts at temperatures exceeding 1,000 °C, the machine's enhanced capacity is opening up new opportunities to produce high-integrity parts larger, and faster, than ever before. As part of a system that simplifies operation and maximizes output, Spectra H is the EBM evolution that's helping the industry take the next step forward.

Designed to produce high heat for crack prone materials

The expanded build chamber, 39% larger than the previous generation EBM machine, allows Spectra H to deliver market-leading, high-temperature production. Movable heat shields create improved insulation, forming the ideal environment for exceptional part production. An auto-calibrated, 6 kW beam provides a 100% increase in power to provide up to 50% faster builds, allowing manufacturers to begin transitioning into high-volume outputs.

With this extended platform, it's possible to print larger parts than ever before, and produce more parts at one time. And with Spectra H's high-heat capability, users can incorporate new alloys into production to expand their offerings, including high-temperature, crack-prone materials.



Spectra H features

- 39% larger build volume than previous generation EBM machines
- Capable of working with high-temperatures and crack-prone materials such as TiAl
- Movable heat shields for improved temperature management
- Auto-calibrated beam for precise part production
- Closed-loop system to maintain powder integrity
- Powder distribution system delivers even layer of powder for optimal part production

INTEGRATED APPROACH FOR BEST RESULTS

The Spectra H features a powerful, integrated hardware and software system for efficient operation of your EBM machine and better build analysis.

- The Spectra H includes Arcam EBM xQam™ technology for high-precision beam autocalibration, a powerful software platform, and electronics for efficient and accurate beam control.
- Arcam EBM LayerQam[™], a camera-based monitoring system, provides for inline part quality verification and comprehensive defect diagnosis. Detailed reports are generated from the data collected by the software after the build is completed. The user is then informed of any defect present and location within the build.

CLOSED-LOOP POWDER-HANDLING SYSTEM MAINTAINS POWDER INTEGRITY

The Spectra H machine is supported by a closed powder handling system that maintains the powder batch integrity. The system is automated and includes a Powder Recovery Station (PRS), an auto dosing sieve and a hopper filler station.

When a built part is cleaned in the PRS, excess powder is recovered and smaller particles are removed in a cyclone separator. Powder also passes through a magnetic sieve to remove any metallic satellites picked up in the cleaning process. The recovered powder is then returned to

the hoppers via the hopper filler station.

And because Spectra H operates within a closed-loop system that creates a dust-tight environment, powders are completely contained and never cross-contaminated or exposed to external elements.



Powder handling equipment

A complete powder handling system to support the additive process, both pre- and post-build:

Powder Recovery Station (PRS)	Vacuum cleaners	Sieving station	Hopper filling station	Trolleys
Recovers unused powder in a closed environment	Clean the finished build	Filters unused powder to rid of oversized particles	Loads sieved powder from barrels into machine hopper	Transport build tank, powder hoppers, and barrels

Arcam EBM Spectra H

Technical data

Max. build size 250 x 430 mm (D,H)

Max. beam power 6kW

Cathode typeSingle crystallineMinimum chamber pressure5 x 10-4mbar

Typical build atmosphere 4 x 10-3mbar (partial pressure of He)

Power supply 3 x 400 V, 32A, 13kVA

He consumption, build process 5 liter/h

He consumption, ventilation 150-200l/build **Typical process temperature range** 600-1,100°C

Size 1,328 x 2,344 x 2,858 mm (D,W,H)

Weight 2,915kg
CAD interface Standard STL

Materials available

- Arcam EBM TiAl, D-Mtrl
- Arcam EBM Nickel Alloy 718, D-Mtrl
- Arcam EBM Highly Alloyed Tool Steel, D-Mtrl
- Arcam EBM Ti6Al4V Grade 5, P-Mtrl





GE Additive