


GE Lighting Adds 150 New U.S. Manufacturing Jobs



Bucyrus Lamp Plant

70 new jobs

- 330 employees currently
- Products made: T8 and T12 linear fluorescent lamps
- 30 miles east of Mansfield, OH
- Opened in 1942



Circleville Lamp Plant

50 new jobs


- 219 employees currently
- Products made: T8 and T12 linear fluorescent lamps and Biax® plug-in CFLs
- 30 miles south of Columbus, OH
- Opened in 1948



Mattoon Lamp Plant

30 new jobs

- 205 employees currently
- Products made: MR16, Automotive, Halogen PAR, HIR and Energy-Efficient Soft White lamps
- 50 miles south of Champaign, IL
- Opened in 1946



Total U.S. Manufacturing Locations

More than half of GE Lighting's manufacturing facilities are in the U.S., including global manufacturing centers of excellence in Ohio, Illinois and North Carolina.



U.S. Plant Locations:

Boulder, CO
Mattoon, IL
Lexington, KY
Somerset, KY
Hendersonville, NC

Bucyrus, OH
Circleville, OH
Cleveland, OH
Dover, OH
Euclid, OH

Logan, OH
Ravenna, OH
Warren, OH
Bridgeville, PA

U.S. Distribution Centers:

Mira Loma, CA
Batesville, IN
Ravenna, OH

★ GE Lighting Global Headquarters, Nela Park, East Cleveland, OH



GE imagination at work